

CAT. N° 6 614 31


**EMERGENCY LUMINAIRE B65 - STANDARD MAINTAINED /
NON MAINTAINED - 100 LM - 1H - LED**

Pack (number of units)	1
Volume (dm ³)	2,332
Weight (g)	689,00

Product characteristics
Standard luminaires - Maintained/Non-maintained (M/NM)

- Standard luminaires require normal lighting manual switching off in order to test emergency lighting
- These Maintained luminaires can also operate in Non-maintained mode according to the wiring of normal lighting
- 100 lm - 1h (LEDs)

General characteristics
B65 LED - weatherproof self-contained emergency lighting luminaire LED

- Weatherproof LED maintained and non-maintained units
- Certified to IEC and EN 60598-2-22 standards
- High power LEDs. IP 65 - IK 07
- Plug-in base to ease fixing, cabling and connection
- Duration: 1 and 3 hours. Ni-Cd or Ni-MH batteries. Recharge time: 24 hours
- Charge monitor with a green LED. Power supply: 230 V ± 10% - 50/60 Hz. Class II
- High-capacity screw terminals (2 x 2.5mm²)
- 3 flexible cable entries for Ø16, 20 and 25 mm tubes
- Can be equipped with metallic protection grids Cat.Nos 0 626 90/92

Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.679\)](#)
- [Description page \(p.686\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

 **Installation & technical data**

- [S000083090EN-3](#)

 **Installation instructions & related documents**

- [LE06963AE](#)

 **Agreements & certificates of conformity**

- [ENEC-ENEC/000993](#)