

CAT. N° 6 616 07



## EMERGENCY LUMINAIRE U21 - STANDARD MAINTAINED / NON MAINTAINED - 350 LM - 1H - LED

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,775
Weight (g)	611,00

### Product characteristics

#### Standard luminaires

- Require normal lighting manual switching off in order to test emergency lighting

#### Maintained/Non-maintained (M/NM)

- Can also operate in Non-maintained mode according to the wiring of normal lighting
- 350 lm - 1h (LEDs)

### General characteristics

#### U21 LED - indoor self-contained emergency lighting luminaires LED

- LED maintained and Non-maintained units
- Certified to IEC and EN60598-2-22 standards
- High power LEDs
- IP 42 - IK 04. Duration: 1 and 3 hours. Ni-Cd or Ni-MH batteries
- Recharge time: 24 hours. Charge monitor with a green LED
- Power supply: 230 V~ ±10% - 50/60Hz - Class II
- High capacity screw terminals (2 x 2.5 mm<sup>2</sup>)
- To install a full IP 65 solution, add IP 65 weatherproof box Cat.No 6 616 16
- Flush-mounting in dry partitions (ceiling and wall): add flush-mounting frame Cat.No 6 617 20. Flush-mounting in masonry (brick or concrete wall): add both flush-mounting box Cat.No 0 617 21 and flush-mounting frame Cat.No 6 617 20
- Can be equipped with metallic protection grids Cat.Nos 0 626 90/92

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.678\)](#)
- [Description page \(p.685\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

#### Agreements & certificates of conformity

- [ENEC - ENEC/000992](#)

#### Installation instructions & related documents

- [LE06909AG](#)