

CAT. N° 6 616 33



EMERGENCY LUMINAIRE URA ONE - STANDARD MAINTAINED/NON MAINTAINED - 1H - 200 LM - LED

Pack (number of units)	1
Volume (dm ³)	1,236
Weight (g)	476,00

Product characteristics

Standard luminaires

- Require normal lighting manual switching off in order test emergency lighting

Maintained/Non-maintained (M/NM)

- Can also operate in Non-maintained mode according to the wiring of normal lighting
- 200 lm - 1h (LEDs)

General characteristics

URA ONE - indoor self-contained emergency lighting luminaire LED

- LED non-maintained and maintained units
- Certified to IEC and EN 60598-2-22 standards
- High power LEDs with optimized lighting distribution
- Low consumption switching power supply. Fully recyclable
- Plug-in back with pre-cutted holes grid to ease installation and maintenance
- Automatic terminals with high capacity: 2 x 2.5mm². IP 42 - IK 07
- Duration: 1 and 3 hours. Ni-Cd or Ni-MH batteries. Recharge time: 24 hours. Charge monitor with a green LED. Opal diffuser
- Power supply: 230 V~ ± 10% - 50/60 Hz. Class II
- Flat flush-mounting integration into ceiling and wall with flush-mounting frame Cat.Nos 6 616 50/51
- Decorative frame to enhance surface-mounting aesthetic integration Cat.Nos 6 616 54/55

Documentation



Catalogue pages & additional information

- [Selection chart \(p.678\)](#)
- [Description page \(p.681\)](#)
- [Technical page \(p.682\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)



Agreements & certificates of conformity

- [ENEC-ENEC/000994](#)



Installation instructions & related documents

- [LE06557AF](#)



Environmental product profile

- [LGRP-00660-V01](#)