

CAT. N° 6 618 61



STANDARD LUMINAIRES NON-MAINTAINED URASPOT EMERGENCY LIGHTING SPOTLIGHT FOR OPEN AREAS AND ANTIPANIC - 200 LM - 1 HOUR

Pack (number of units)	1
Volume (dm ³)	1,544
Weight (g)	277,00

Product characteristics

Standard luminaires non-maintained (NM)

200 lm - 1 h

- For open areas and antipanic

General characteristics

URASPOT - LED emergency lighting spotlights for ceiling

- Non-maintained self-contained emergency lighting units
- Certified to IEC and EN 60598-2-22 standards
- High power LED with high performance lens specially designed:
 - to optimize lighting distribution on the floor
 - to increase spacing for installation
- Low consumption switching power supply
- Duration: 1 and 3 hours
- Ni-Cd batteries
- Charge monitor with green LED
- Recharging time: 18 hours
- Power supply: 230 V~ ± 10%- 50/60 Hz. Class II - IP 40 - IK 04
- Screwless terminal blocks: 2 x 1,5 mm²

Documentation

Catalogue pages & additional information

- [Selection chart \(p.678\)](#)
- [Description page \(p.680\)](#)

Agreements & certificates of conformity

- [QC / CB-ES2003](#)

Installation instructions & related documents

- [LE09715AD](#)