

CAT. N° 6 676 52



DRX 630 ADJUSTABLE THERMAL MAGNETIC MCCB - BREAKING CAPACITY ICU 36 KA - 415 V~ - 3P - IN 500 A

Pack (number of units)	1
Volume (dm ³)	7,459
Weight (g)	5 670,00

Product characteristics

DRX 630

- Thermal adjustable from 0.8 to 1 x I_n
- Magnetic adjustable from 5 to 10 x I_n

Breaking capacity I_{cu} 36 kA (415 V~)

- 3P
- 500 A

General characteristics

DRX™ 630 adjustable - thermal magnetic MCCBs from 320 to 630 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - Screw terminals
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Adjustable thermal and magnetic
- Conform to IEC 60947-2

Documentation



Catalogue pages & additional information

- [Description page \(p.131\)](#)
- [Technical page \(p.132\)](#)
- [Technical page \(p.133\)](#)
- [DRXTM 630 adjustable](#)



Installation & technical data

- [F02406EN00_DRX630_adjENG_v2](#)



Installation instructions & related documents

- [LE07105AA](#)