

CAT. N° 6 676 58



## DRX 630 ADJUSTABLE THERMAL MAGNETIC MCCB - BREAKING CAPACITY Icu 50 KA - 415 V~ - 3P - IN 320 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	7,459
Weight (g)	4 949,00

### Product characteristics

#### DRX 630

- Thermal adjustable from 0.8 to 1 x I<sub>n</sub>
- Magnetic adjustable from 5 to 10 x I<sub>n</sub>

#### Breaking capacity I<sub>cu</sub> 50 kA (415 V~)

- 3P
- 320 A

### General characteristics

#### DRX™ 630 adjustable - thermal magnetic MCCBs from 320 to 630 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - Screw terminals
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Adjustable thermal and magnetic
- Conform to IEC 60947-2

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.131\)](#)
- [Technical page \(p.132\)](#)
- [Technical page \(p.133\)](#)
- [DRXTM 630 adjustable](#)



#### Installation & technical data

- [F02406EN00\\_DRX630\\_adjENG\\_v2](#)



#### Installation instructions & related documents

- [LE07105AA](#)