

CAT. N° 6 676 58

**DRX 630 ADJUSTABLE THERMAL MAGNETIC MCCB -  
BREAKING CAPACITY ICU 50 KA - 415 V~ - 3P - IN 320 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	7,459
Weight (g)	4 949,00

**Product characteristics****DRX 630**

- Thermal adjustable from 0.8 to 1 x In
- Magnetic adjustable from 5 to 10 x In

**Breaking capacity Icu 50 kA (415 V~)**

- 3P
- 320 A

**General characteristics****DRX™ 630 adjustable - thermal magnetic MCCBs  
from 320 to 630 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - Screw terminals
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Adjustable thermal and magnetic
- Conform to IEC 60947-2

**Documentation****Catalogue pages & additional information**

- [Description page \(p.131\)](#)
- [Technical page \(p.132\)](#)
- [Technical page \(p.133\)](#)
- [DRXTM 630 adjustable](#)