

CAT. N° 6 695 03



## AIR CIRCUIT BREAKER DMX-SP 2500 FIXED VERSION - BREAKING CAPACITY 42KA - 3P - 1250A

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Fixed version

- Supplied with:
  - 4 auxiliary contacts: NO/NC
  - door sealing

#### Breaking capacity Icu 42 kA (415 V~)

- Frame 2500
- 3P
- In : 1250 A

### General characteristics

#### Air circuit breakers DMX-SP 2500 - from 630 to 2500 A

- Automatic air circuit breakers must be equipped with DMX-SP 2500 electronic protection units Cat.No 0 281 64/65/66/67/68, imperatively ordered together for factory assembly
- Please ask for DMX-SP order form
- Conform to IEC 60947-2

### Documentation

#### Installation instructions & related documents

- [LE09882AB](#)

#### Installation & technical data

- [F02472EN\\_04\\_DMX\\_SP2500\\_v01](#)
- [LE11610AA](#)