

CAT. N° 6 695 07

**AIR CIRCUIT BREAKER DMX-SP 2500 FIXED VERSION -
BREAKING CAPACITY 42KA - 4P - 800A**

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics**Fixed version**

- Supplied with:
 - 4 auxiliary contacts: NO/NC
 - door sealing

Breaking capacity Icu 42 kA (415 V~)

- Frame 2500
- 4P
- In : 800 A

General characteristics**Air circuit breakers DMX-SP 2500 - from 630 to 2500 A**

- Automatic air circuit breakers must be equipped with DMX-SP 2500 electronic protection units Cat.No 0 281 64/65/66/67/68, imperatively ordered together for factory assembly
- Please ask for DMX-SP order form
- Conform to IEC 60947-2

Documentation **Installation instructions & related documents**

- [LE09882AB](#)

 **Installation & technical data**

- [F02472EN_04_DMX_SP2500_v01](#)
- [LE11610AA](#)