

CAT. N° 6 696 43



AIR CIRCUIT BREAKER DMX-SP 4000 DRAW-OUT VERSION - BREAKING CAPACITY 50KA - 4P - 4000A

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Draw-out version

- Supplied with:
 - 1 auxiliary contact: NO/NC
 - door sealing
- To be installed on a draw-out base Cat.No 6 696 12 or 6 696 13

Breaking capacity Icu 50 kA (415 V~)

- Frame 4000
- 4P
- In : 4000 A

General characteristics

Air circuit breakers DMX-SP 4000 - from 3200 to 4000 A

- Automatic air circuit breakers must be equipped with DMX-SP 4000 electronic protection units Cat.No 6 682 90/91/92 and 0 288 00/01/02, imperatively ordered together for factory assembly
- Please ask for DMX-SP order form
- Conform to IEC 60947-2

Documentation

Installation instructions & related documents

- [LE11403AA](#)
- [LE11754AA](#)

Installation & technical data

- [F03071EN03_DMX_SP_4000](#)