

CAT. N° 6 696 44



## AIR CIRCUIT BREAKER DMX-SP 4000 DRAW-OUT VERSION - BREAKING CAPACITY 65KA - 3P - 3200A

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Draw-out version

- Supplied with:
  - 1 auxiliary contact: NO/NC
  - door sealing
- To be installed on a draw-out base Cat.No 6 696 12 or 6 696 13

#### Breaking capacity Icu 65 kA (415 V~)

- Frame 4000
- 3P
- In : 3200 A

### General characteristics

#### Air circuit breakers DMX-SP 4000 - from 3200 to 4000 A

- Automatic air circuit breakers must be equipped with DMX-SP 4000 electronic protection units Cat.No 6 682 90/91/92 and 0 288 00/01/02, imperatively ordered together for factory assembly
- Please ask for DMX-SP order form
- Conform to IEC 60947-2

### Documentation

#### Installation instructions & related documents

- [LE11403AA](#)
- [LE11404AA](#)
- [LE11754AA](#)

#### Installation & technical data

- [F03071EN03\\_DMX\\_SP\\_4000](#)