

CAT. N° 6 697 08

**THERMAL MAGNETIC MCCB DRX 125 HP ADJUSTABLE -  
BREAKING CAPACITY 25KA - 3P - 100A**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****DRX 125 HP**

- Thermal adjustable from 0.8 to 1 x In

**Breaking capacity Icu 25 kA (415 V~)**

- 3P
- In : 100 A

**General characteristics****DRX™ 125 HP adjustable - thermal magnetic MCCBs  
from 16 to 125 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P)
- Adjustable thermal
- Fixed magnetic
- Conform to IEC 60947-2

**Documentation** **Installation instructions & related documents**

- [LE10799AA](#)