

CAT. N° 6 697 12

**THERMAL MAGNETIC MCCB DRX 125 HP ADJUSTABLE -
BREAKING CAPACITY 25KA - 4P - 25A**

| | |
|---------------------------|-----|
| Pack (number of units) | O/R |
| Volume (dm ³) | O/R |
| Weight (g) | O/R |

Product characteristics**DRX 125 HP**

- Thermal adjustable from 0.8 to 1 x In

Breaking capacity Icu 25 kA (415 V~)

- 4P
- In : 25 A

General characteristics**DRX™ 125 HP adjustable - thermal magnetic MCCBs
from 16 to 125 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P)
- Adjustable thermal
- Fixed magnetic
- Conform to IEC 60947-2

Documentation **Installation instructions & related documents**

- [LE10799AA](#)