

CAT. N° 6 946 05



MULTI-OUTLET EXTENSION - GERMAN STANDARD - 4X2P+E - SWITCHED - 3 M CORD - BLACK

Pack (number of units)	5
Volume (dm ³)	21,384
Weight (g)	3 694,00

Product characteristics

Multi-outlet extensions - switched

- On/off switch with a light indicator, can be operated by foot or by hand
- Socket with child protection shutters tested to withstand 10000 operations
- Orientable socket outlets
- Maximum space between 2 sockets to connect transfos, chargers, etc.
- Supplied with self-gripping tie for grouping the cords of the connected devices
- Direct wall-mounting possibilities (with screws)
- Cable management possible around the wall-mounting fixtures
- With power supply cord 1.5 m (3G 1.5 mm²) or 3 m (3G 1.5 mm²)
- 16 A max. - Power 3500 W at 230 V

3 m cord

- Black
- 4 x 2P+E

General characteristics

Multi-outlet extensions with cord - German standard

- To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
- Extra-flat (only 30 mm thick): can be slid underneath furniture

Documentation



Catalogue pages & additional information

- [Description page \(p.640\)](#)



Agreements & certificates of conformity

- MEEI - UP 69261357 0001
- OC / CB - FR 698411