

CAT. N° 6 950 10

**MULTI-OUTLET EXTENSION - GERMAN STANDARD -
3X2P+E - UNSWITCHED - 1.5 M CORD - BLACK**

Pack (number of units)	10
Volume (dm ³)	12,286
Weight (g)	3 578,00

Product characteristics**Multi-outlet extensions - unswitched**

- Wall-mounting possibilities with the packaging accessory
- 90° socket for connecting a transformer without blocking another socket
- Power supply cord 1.5 m (3G 1.5 mm²) or 3 m (3G 1.5 mm²) or 5 m (3G 1.5 mm²)
- 16 A max. power 3 500 W at 230 V

1.5 m cord

- Black
- 3 x 2P+E

General characteristics**Multi-outlet extensions with cord - German standard**

- To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
- Extra-flat (only 30 mm thick): can be slid underneath furniture

Documentation**Catalogue pages & additional information**

- [Description page \(p.640\)](#)

**Agreements & certificates of conformity**

- OVE - 131-261-09
- OC / CB - 687773D
- MEEI - UP 69254786 0001