

CAT. N° 6 984 14

**BRITISH STANDARD MULTI-OUTLET EXTENSION - 4X2P+E
- ONE SWITCH PER SOCKET - 5 M CORD**

Pack (number of units)	1
Volume (dm ³)	4,196
Weight (g)	847,00

Product characteristics**Multi-outlet extensions**


- Conform to BS 1363 - ASTA certification
- Sockets equipped with shutter for child protection
- Can be wall, desk or floor mounted thanks to key holes at the back
- Flame-retardant material (up to 850°C)
- Overload protection by fuse (integrated)
- Power supply cord 3m or 5m, with 1.25 mm² section
- 13 A max. Power: 3250 W at 250 V - 50/60 Hz

5 m cord – with one switch per socket

- On/Off single pole power switch, with light indicator
- ESMA certification
- White/Grey
- 4 x 2P+E

General characteristics**Multi-outlet extensions with cord - British standard**

- To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
- Extra-flat (only 30 mm thick): can be slid underneath furniture

Documentation **Catalogue pages & additional information**

- [Description page \(p.638\)](#)

 **Agreements & certificates of conformity**

- [ASTA - 1247](#)