

CAT. N° 6 985 15



BRITISH STANDARD MULTI-OUTLET EXTENSION - 5X2P+E - ONE SWITCH PER SOCKET - 5 M CORD - WHITE/GREY

| | |
|---------------------------|----------|
| Pack (number of units) | 5 |
| Volume (dm ³) | 24,381 |
| Weight (g) | 5 239,00 |

Product characteristics

Multi-outlet extensions

- Conform to BS 1363 - ASTA and G-mark certifications
- Sockets equipped with shutter for child protection
- Can be wall, desk or floor mounted thanks to key holes at the back
- Flame-retardant material (up to 850°C)
- Overload protection by fuse (integrated into the molded plug)
- 13 A max. Power: 3250 W at 250 V - 50/60 Hz

5 m cord – with one switch per socket

- On/Off single pole power switch, with light indicator
- ECAS certification
- Power supply cord with 1.25 mm² section
- White/Grey
- 5 x 2P+E

General characteristics

Multi-outlet extensions with cord - British standard

- To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
- Extra-flat (only 30 mm thick): can be slid underneath furniture

Documentation



Installation & technical data

- [F03664EN-00](#)



Agreements & certificates of conformity

- [ASTA-1247](#)