

CAT. N° 6 985 20



**BRITISH STANDARD MULTI-OUTLET EXTENSION WITH 2
USB PORTS TYPE A - 4X2P+E -ONE SWITCH PER SOCKET
-3 M CORD -WHITE/GREY**

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R


Product characteristics

Multi-outlet extensions with 2 USB ports type A - 2.4 A 12 W
3 m – with one switch per socket
 ■ 4 x 2P+E White/Grey

General characteristics

Multi-outlet extensions with cord - British standard
 ■ To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
 ■ Extra-flat (only 30 mm thick): can be slid underneath furniture

Documentation

 **Catalogue pages & additional information**

- [Description page \(p.638\)](#)

 **Agreements & certificates of conformity**

- [ASTA-1247](#)

 **Installation & technical data**

- [F03664EN-00](#)