

CAT. N° 6 985 30

**BRITISH STANDARD MULTI-OUTLET EXTENSION WITH 2  
USB PORTS TYPE A - 4X2P+E - ONE SWITCH PER CORD -  
3 M CORD -WHITE/GREY**


Pack (number of units)	10
Volume (dm <sup>3</sup> )	45,05
Weight (g)	8 877,00

**Product characteristics****Multi-outlet extensions with 2 USB ports type A - 2.4 A 12 W****3 m – with one switch per extension cord**

- 4 x 2P+E White/Grey

**General characteristics****Multi-outlet extensions with cord - British standard**

- To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
- Extra-flat (only 30 mm thick): can be slid underneath furniture

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.638\)](#)

 **Agreements & certificates of conformity**

- [ASTA-1247](#)

 **Installation & technical data**

- [F03664EN-00](#)