

CAT. N° 6 985 35

**BRITISH STANDARD MULTI-OUTLET EXTENSION - 5X2P+E
- ONE SWITCH PER CORD - 5 M CORD - WHITE/GREY**

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics**Multi-outlet extensions**

- Conform to BS 1363 - ASTA and G-mark certifications
- Sockets equipped with shutter for child protection
- Can be wall, desk or floor mounted thanks to key holes at the back
- Flame-retardant material (up to 850°C)
- Overload protection by fuse (integrated into the molded plug)
- 13 A max. Power: 3250 W at 250 V - 50/60 Hz

5 m cord – with one switch per extension cord

- On/Off double pole safety switch, with light indicator
- SASO and SQM certifications
- Overload protection by circuit breaker integrated into the body of the product, equipped with a "Reset" push button
- Power supply cord with 1.5 mm² section
- White/Grey
- 5 x 2P+E

General characteristics**Multi-outlet extensions with cord - British standard**

- To connect several devices equipped with plugs with or without earth: appliances class I (simple insulation) or class II (double insulation), lamps, PC, TV, stereo, etc.
- Extra-flat (only 30 mm thick): can be slid underneath furniture

Documentation**Installation & technical data**

- [F03664EN-00](#)

**Agreements & certificates of conformity**

- [ASTA-1247](#)