

CAT. N° 6 998 11



OMNIREX T-PLUG-IN TIME SWITCH-24-HOUR PROGRAMME-GERMAN STANDARD-SWITCHING STEP 15 MIN

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,887 |
| Weight (g) | 129,00 |

Product characteristics

OmniRex - Plug-in time switches

- Manuel switch ON - Auto
- With 2P+T plug and 10/16 A socket base and 16 A socket
- With child protection
- Override/manual switch
- Mains hold accuracy
- Synchronous motor, 230 V, 50 Hz
- 1 contact NO 250 V/50 Hz, 16 A- $\cos \varphi = 1$

OmniRex T - 24-hour programme

- German standard - With child protection
- Switching step 15 min
- Mini switching time 15 min
- Switching accuracy ± 5 min
- German standard - With child protection
- Switching step 15 min
- Mini switching time 15 min
- Switching accuracy - 5 min

General characteristics

Analogue time switches

- Power supply 230 V~
- Override switching "ON" or "OFF" in front face
- 1 output via changeover contact
- (2 changeover contacts for Cat.No 0 499 26)

Documentation



Catalogue pages & additional information

- [Description page \(p.092\)](#)
- [Dimensions of din-rail equipment](#)
- [Analogue time switches - MicroRex Plus 2 time switches](#)



Agreements & certificates of conformity

- [OC / CB-37482](#)
- [VDE-40022079](#)



Installation instructions & related documents

- [notice_699811](#)



Environmental product profile

- [LGRP-00345-V01](#)