

CAT. N° 6 998 12



OMNIREX W-PLUG-IN TIME SWITCH-7-DAY PROGRAMME-GERMAN STANDARD-SWITCHING STEP 2 HOURS

Pack (number of units)	1
Volume (dm ³)	0,887
Weight (g)	131,00

Product characteristics

OmniRex - Plug-in time switches

- Manuel switch ON - Auto
- With 2P+T plug and 10/16 A socket base and 16 A socket
- With child protection
- Override/manual switch
- Mains hold accuracy
- Synchronous motor, 230 V, 50 Hz
- 1 contact NO 250 V/50 Hz, 16 A- $\cos \varphi = 1$

OmniRex W - 7-day programme

- German standard - With child protection
- Switching step 2 hours
- Mini switching time 2 hours
- Switching accuracy ± 30 min
- German standard - With child protection
- Switching step 2 hours
- Mini switching time 2 hours
- Switching accuracy - 30 min

General characteristics

Analogue time switches

- Power supply 230 V~
- Override switching "ON" or "OFF" in front face
- 1 output via changeover contact
- (2 changeover contacts for Cat.No 0 499 26)

Documentation

Catalogue pages & additional information

- [Description page \(p.092\)](#)
- [Dimensions of din-rail equipment](#)
- [Analogue time switches - MicroRex Plus 2 time switches](#)

Agreements & certificates of conformity

- [OC / CB-37482](#)
- [VDE-40022079](#)

Installation instructions & related documents

- [notice_699812](#)

Environmental product profile

- [LGRP-00345-V01](#)