

CAT. N° 7 300 03



SINGLE POLE SWITCH SYNERGY - 3 GANG - 2 WAY - 10 AX 250 V~ - WHITE

Pack (number of units)	10
Volume (dm ³)	2,321
Weight (g)	946,00

Product characteristics

Single pole plate switches 10 AX - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep
- ASTA licence

Nominal plate dimensions: 86 x 86 mm

- 3 gang - 2 way

General characteristics

Synergy™ - single pole switches, single pole push and key switches, rotary dimmers - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

Documentation

Catalogue pages & additional information

- [Description page \(p.579\)](#)

Agreements & certificates of conformity

- [ASTA-781](#)
- [QC / CB-FR_708093](#)

Installation & technical data

- [F00223EN-03](#)

Environmental product profile

- [LGRP-2015-309-V1-EN](#)

NEW : ANTIBACTERIAL



Made of material which has intrinsic antimicrobial properties