

REF . 7 300 04

**SINGLE POLE SWITCH SYNERGY - 4 GANG - 2 WAY - 10 AX
250 V~ - WHITE**

Emballage (nombre number of units)	5
Volume (dm ³)	2,321
Poids (g)	721,00

Caractéristiques du produit**Single pole plate switches 10 AX - 250 V~**


- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep
- ASTA licence

Nominal plate dimensions: 86 x 146 mm

- 4 gang - 2 way

Caractéristiques générales**Synergy™ - single pole switches, single pole push
and key switches, rotary dimmers - white**

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

Documentation associée **Catalogue pages & additional information**

- [Description page \(p.579\)](#)

 **Agreements & certificates of conformity**

- [ASTA-781](#)
- [QC / CB-FR_708093](#)

 **Installation & technical data**

- [F00223EN-03](#)

 **Environmental product profile**

- [LGRP-2015-309-V1-EN](#)

NEW : ANTIBACTERIAL

Made of material which has intrinsic antimicrobial properties