

CAT. N° 7 300 75



SOCKET OUTLET SYNERGY - 2 GANG UNSWITCHED - 13 A 250 V~ - WHITE

Pack (number of units)	5
Volume (dm ³)	2,955
Weight (g)	891,00

Product characteristics

Socket outlets 13 A - 250 V~

- Conform to BS 1363: Part. 2
- For flush-mounting, back box to be min. 25 mm deep
- With safety shutter mechanism
- ASTA licence

Unswitched

- 2 gang
- Nominal plate dimensions: 86 x 146 mm

General characteristics

Synergy™ - British standard socket outlets - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

Documentation

Catalogue pages & additional information

- [Description page \(p.581\)](#)

Agreements & certificates of conformity

- [ASTA-780](#)
- [G-MARK-LVE/2020/000865](#)

Installation & technical data

- [F00167EN-00](#)

NEW : ANTIBACTERIAL



Made of material which has intrinsic antimicrobial properties