

CAT. N° 7 300 79



## SOCKET OUTLET WITH USB CHARGER SYNERGY - SINGLE POLE SWITCHED - 2 GANG - WHITE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,729
Weight (g)	220,00

### Product characteristics

#### Socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2
- USB charger conform to IEC 60950-1

#### Single pole switched

- 2 gang
- USB Type-A + Type-C™ 3 A - 5 VDC - 15 W
- Consumption in passive mode less than 0.08 W

### General characteristics

#### Synergy™ - British standard socket outlets - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.581\)](#)

#### Agreements & certificates of conformity

- [OC / CB-SE-88178M1](#)
- [OC / CB-SE-102292](#)
- [OC / CB-SE-104641](#)
- [G-MARK-0048202100032/A1](#)

#### Installation & technical data

- [F02762EN-01](#)

### NEW : ANTIBACTERIAL



Made of material which has intrinsic antimicrobial properties