

CAT. N° 7 300 86



## SOCKET OUTLET SYNERGY - 2 GANG UNSWITCHED SASO - 15 A - 127 V~ - WHITE

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 5      |
| Volume (dm <sup>3</sup> ) | 2,925  |
| Weight (g)                | 776,00 |

### Product characteristics

#### Socket outlets 15 A - 127 V~

- Standard terminal screws
- For flush-mounting, back box to be min. 35 mm deep
- 2 gang unswitched
- Nominal plate dimensions: 86 x 146 mm

### General characteristics

#### Synergy™ - British standard socket outlets - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.582\)](#)



#### Installation & technical data

- [F00275EN-00](#)