

CAT. N° 7 300 89



SOCKET OUTLET SYNERGY - 1 GANG SWITCHED - 15 A 250 V~ - WHITE

Pack (number of units)	10
Volume (dm ³)	4,055
Weight (g)	1 089,00

Product characteristics

Socket outlets 15 A - 250 V~

- Conform to BS 546
- Patented 3 pin safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm
- 1 gang - switched, single pole


General characteristics

Synergy™ - British standard socket outlets - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

Documentation

 **Catalogue pages & additional information**
 ■ [Description page \(p.582\)](#)

 **Installation & technical data**
 ■ [F00164EN-00](#)

NEW : ANTIBACTERIAL



Made of material which has intrinsic antimicrobial properties