

CAT. N° 7 301 07



**SINGLE PUSH SWITCH SYNERGY - 1 GANG - 2 WAY BELL SYMBOL - 10 AX 250 V~ - WHITE**

Pack (number of units)	5
Volume (dm <sup>3</sup> )	1,567
Weight (g)	447,00

**Product characteristics**

**Single pole push switches 10 A - 250 V~**

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep
- ASTA licence
- 1 gang - 2 way push switch with bell symbol

**General characteristics**

**Synergy™ - single pole switches, single pole push and key switches, rotary dimmers - white**

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.579\)](#)

**Agreements & certificates of conformity**

- [ASTA-781](#)
- [QC / CB-FR\\_708093](#)

**Installation & technical data**

- [F00222EN-01](#)

**NEW : ANTIBACTERIAL**



Made of material which has intrinsic antimicrobial properties