

REF . 7 301 32

**SINGLE POLE SWITCH SYNERGY - 2 GANG - 2 WAY 20 AX  
250 V~ - WHITE**

Emballage (nombre number of units )	10
Volume (dm <sup>3</sup> )	2,321
Poids (g)	904,00

**Caractéristiques du produit****Single pole plate switches 20 AX - 250 V~**

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep
- Nominal plate dimensions: 86 x 86 mm
- 2 gang - 2 way

**Caractéristiques générales****Synergy™ - single pole switches, single pole push and key switches, rotary dimmers - white**

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

**Documentation associée** **Catalogue pages & additional information**

- [Description page \(p.579\)](#)

 **Agreements & certificates of conformity**

- [ASTA-782](#)
- [QC / CB-FR\\_708093](#)

 **Installation & technical data**

- [F03162EN-00](#)

**NEW : ANTIBACTERIAL**

Made of material which has intrinsic antimicrobial properties