

CAT. N° 7 338 71



DOUBLE POLE SOCKET OUTLET SYNERGY - 2 GANG SWITCHED + LED - 13 A 250 V~ - METALCLAD

| | |
|---------------------------|----------|
| Pack (number of units) | 5 |
| Volume (dm ³) | 4,398 |
| Weight (g) | 2 643,00 |

Product characteristics

Double pole socket outlets 13 A - 250 V~

- Conform to BS 1363 - Part 2: 1995
- With safety shutter mechanism
- Flush-mounting back box: min. 25 mm deep

Switched with red LED power indicator

- 2 gang
- Nominal plate dimensions: 86 x 146 mm

General characteristics

Synergy™ - British standard socket outlets, RCD sockets and fused connection units - Metalclad

- Front plates: grey epoxy coated steel
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Supplied complete with close fit 43 mm deep surface-mounting back box

Documentation

Catalogue pages & additional information

- [Description page \(p.599\)](#)

Agreements & certificates of conformity

- [ASTA - 780](#)

Installation & technical data

- [F02498EN-00](#)