

CAT. N° 7 520 33



ELECTRONIC ROOM THERMOSTAT VALENA IN'MATIC - SCREW/CLAW MOUNTING

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,547 |
| Weight (g) | 115,00 |

Product characteristics

Thermostats

- Screw terminals

Electronic room thermostat

- For direct radiant ceiling panels and underfloor heating
- Option for cooling systems
- Adjustment range: 10 °C to 30 °C
- frost protection 7 °C
- Adjustment precision: 0.5 °C
- 1 potential free changeover contact
- Switching capacity:
 - 8 A ? 250 V~ ? resistive circuit
 - 2 A ? 250 V~ ? inductive circuit
- Power supply: 230 V~ 50/60 Hz
- Adjustable brightness of LEDs

General characteristics

Valena™ IN'MATIC mechanisms - thermostats and ventilation controls

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation



Catalogue pages & additional information

- [Description page \(p.498\)](#)
- [Selection chart \(p.513\)](#)



Installation instructions & related documents

- [LE07426AE](#)