

CAT. N° 7 520 34



FLOOR HEATING THERMOSTAT VALENA IN'MATIC - SCREW/CLAW MOUNTING

Pack (number of units)	1
Volume (dm ³)	1,08
Weight (g)	284,00

Product characteristics

Thermostats

- Screw terminals

Floor heating thermostat

- For floor heating systems
- Adjustment range: 10 °C to 30 °C
- Frost protection 7 °C
- Adjustment precision: 0.5 °C
- 1 potential free N/O contact
- Switching capacity: 16 A ? 250 V~ ? resistive circuit
- Power supply: 230 V~ 50/60 Hz
- Adjustable brightness of LEDs
- Supplied with 4 m floor sensor (max. wire length 20 m)

General characteristics

Valena™ IN'MATIC mechanisms - thermostats and ventilation controls

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation



Catalogue pages & additional information

- [Description page \(p.498\)](#)
- [Selection chart \(p.513\)](#)



Installation instructions & related documents

- [LE07427AE](#)