

CAT. N° 7 520 37



LOCAL CONTROL VALENA IN'MATIC - SOUND DIFFUSION - WITH POWER SUPPLY

Pack (number of units)	1
Volume (dm ³)	0,547
Weight (g)	122,00

Product characteristics

Sound diffusion

Local control with display

- Equipped with an LCD screen, used to select the music source: main (Hi-Fi) or local (e.g.: MP3 player) via cord with Ø3.5mm jack (not supplied)
- Stereo output 2 x 1.5 W
- Volume, balance, bass/treble and loudness controls
- Time display
- Integrated alarm clock function (by beep or music)
- General call function from all local controls with answer possible from the person called (microphone integrated in the product)
- Compatible with 4-8 or 16 ohms

General characteristics

Valena™ IN'MATIC mechanisms - sound diffusion and loudspeakers

- Valena In'Matic mechanisms are with metal support, claw or screw mounting
- To be equipped with cover plates and plates of Valena Life or Valena Allure
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation



Catalogue pages & additional information

- [Description page \(p.507\)](#)
- [Selection chart \(p.511\)](#)
- [Selection chart \(p.515\)](#)
- [Valena™ IN'MATIC mechanisms - sound diffusion](#)



Installation instructions & related documents

- [LE07442AA](#)
- [LE07443AA](#)