

CAT. N° 7 521 34



COVER PLATE VALENA LIFE - FLOOR HEATING THERMOSTAT - WITH MECHANISM - WHITE

Pack (number of units)	1
Volume (dm ³)	1,08
Weight (g)	289,00

Product characteristics

Thermostats

- Screw terminals

Floor heating thermostats

- For floor heating systems. Adjustment range: 10 °C to 30 °C. Frost protection 7 °C
- Adjustment precision: 0.5 °C
- 1 potential free N/O contact;
- Switching capacity: 16 A - 250 V~ - resistive circuit
- Power supply: 230 V~ 50/60 Hz
- Adjustable brightness of LEDs
- Supplied with 4 m floor sensor (max. wire length 20 m)
- White

General characteristics

Valena™ Life - motion sensors, roller blind controls and thermostats with cover plate

- Valena In'Matic mechanisms supplied with cover plates and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation



Catalogue pages & additional information

- [Selection chart \(p.509\)](#)
- [Description page \(p.519\)](#)



Installation & technical data

- F03355EN-00



Installation instructions & related documents

- [LE07427AE](#)