

REF . 7 521 56

**TWO-WAY SWITCH VALENA LIFE - 10 AX 250 V~ - IP44 - WITH COVER PLATE - WHITE**

Emballage (nombre number of units)	5
Volume (dm ³)	2,668
Poids (g)	435,00

Caractéristiques du produit**Switches 10 AX- 250 V~**

- Automatic terminals

Two-way switch

- White

Caractéristiques générales**Valena™ Life - IP44 devices with white cover plate**

- Valena In'Matic mechanisms supplied with white cover plates, weatherproof membrane and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation associée**Catalogue pages & additional information**

- [Description page \(p.525\)](#)

**Installation & technical data**

- [F02085EN-00](#)

**Installation instructions & related documents**

- [LE08107AA](#)
- [LE08107AC](#)

**Agreements & certificates of conformity**

- [OC / CB-FR_711212](#)
- [VDE-40044639](#)