

REF . 7 521 60


ROTARY DIMMER VALENA LIFE - 240 V~ - 50 HZ - WITH COVER PLATE - WHITE


Emballage (nombre number of units)	1
Volume (dm ³)	0,824
Poids (g)	156,00

Caractéristiques du produit
Dimmers 240 V~ - 50 Hz

- Equipped with overvoltage and short-circuit protection
- When switched on, lights up at the level set before last switch-off
- Can be remotely controlled via non-illuminated push-buttons (Cat.No 7 520 11), with each push-button able to perform the ON/OFF and dimming function

Rotary dimmer without neutral

- For all types of lamps:
 - dimmable LEDs: 5 W to 75 W (10 lamps max.)
 - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.)
 - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA
 - fluorescent tube - ballast: 5 VA to 300 VA
 - halogen and incandescent 240 V~ : 5 W to 300 W
- When switched on, gradually (2 seconds) lights up at the level set before last switch-off
- White

Caractéristiques générales
Valena™ Life - dimmers with cover plate

- Valena In'Matic mechanisms supplied with cover plates and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation associée
 **Catalogue pages & additional information**

- [Description page \(p.518\)](#)

 **Installation & technical data**

- [F01954EN-02](#)

 **Installation instructions & related documents**

- [LE07432AB_hermes](#)
- [LE07432AC](#)