

CAT. N° 7 521 77



MOTION SENSOR VALENA LIFE - 250 W- IP44 - WITH COVER PLATE - WHITE

Pack (number of units)	1
Volume (dm ³)	0,677
Weight (g)	149,00

Product characteristics

Motion sensor without neutral 250 W IP 44

- Compatible with any type of lamp
- Detection field 120°
- Detection range 8 m
- Integrated self-protection against overloads and short-circuits
- Screw terminals
- Accepted power by lamp type:
 - LEDs 3 W to 100 W (if several sensors are installed on the same circuit, the minimum load increases)
 - compact fluorescent 3 W to 100 W (if several sensors are installed on the same circuit, the minimum load increases)
 - LEDs, CFLs, Halogen, fluorescent tubes with ferromagnetic or electronic ballast: 3 VA to 250 VA
 - 230 V halogen, incandescent: 3 W to 250 W
- Up to 3 sensors can be connected in parallel
- Time delay setting from 10 s to 10 min.
- Light level threshold setting from 5 lux to 1275 lux.
- Standby consumption: 0.02 W
- White

General characteristics

Valena™ Life - IP44 devices with white cover plate

- Valena In'Matic mechanisms supplied with white cover plates, weatherproof membrane and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation

Catalogue pages & additional information

- [Description page \(p.525\)](#)

Installation & technical data

- [F01970EN-01](#)

Installation instructions & related documents

- [LE07972AD](#)
- [LE08107AA](#)
- [LE08107AC](#)