

CAT. N° 7 522 73



MOTION SENSOR WITH NEUTRAL VALENA LIFE - WITH COVER PLATE - IVORY

Pack (number of units)	1
Volume (dm ³)	0,824
Weight (g)	124,00

Product characteristics

Motion sensors

- All sensors are compatible with any type of lamp
- Detection field 120°
- Detection range 8 m
- Integrated self-protection against overloads and short-circuits

Motion sensors with neutral

- Accepted power by lamp type:
 - LEDs: 0 to 50W
 - compact fluorescent: 0 to 50 W
 - LEDs, CFLs, Halogen with ferromagnetic or electronic ballast: 0 to 200 VA
 - fluorescent tubes with ferromagnetic or electronic ballast: 0 to 150 VA
 - 230 V halogen, incandescent: 0 to 400 W
- Only one sensor per circuit
- No remote manual control with push-button
- Time delay setting from 10 s to 10 min.
- Light level threshold setting from 5 lux to 1275 lux
- Standby consumption: 0.55 W
- Ivory

General characteristics

Valena™ Life - motion sensors, roller blind controls and thermostats with cover plate

- Valena In'Matic mechanisms supplied with cover plates and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation

Catalogue pages & additional information

- [Description page \(p.519\)](#)

Installation & technical data

- [F01966EN-03](#)

Installation instructions & related documents

- [LE07972AD](#)