

CAT. N° 7 530 25



2P+E SOCKET VALENA IN'MATIC - SCREW TERMINALS - GERMAN STANDARD - 16 A 250 V~

Pack (number of units)	10
Volume (dm ³)	3,802
Weight (g)	743,00

Product characteristics

German standard socket outlets 16 A - 250 V~

2P+E socket

- Illuminated version with LED Cat.No 0 676 64
- Specific cover for illuminated version, Life and Allure
- Screw terminals

General characteristics

Valena™ IN'MATIC mechanisms - socket outlets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- IP 2X protection
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.502\)](#)
- [Selection chart \(p.511\)](#)
- [Selection chart \(p.515\)](#)

Agreements & certificates of conformity

- [MEEI-UP 69250798 0001](#)
- [MEEI-UP 69248331 0001, 0002, 0003](#)
- [OC / CB-HU-003511](#)
- [OC / CB-HU-001410](#)
- [OC / CB-HU-001784](#)

Installation & technical data

- [F01949EN-01](#)

Environmental product profile

- [LGRP-00774-V01](#)