

REF . 7 530 61


**PASSTHROUGH MALE TV SOCKET VALENA IN'MATIC**


Emballage (nombre number of units )	5
Volume (dm <sup>3</sup> )	1,912
Poids (g)	531,00

**Caractéristiques du produit**
**Passthrough sockets**

- Installation in case of maintenance
- Amplifier and a line balancing are recommended
- TV male connector (Ø9.5 mm): 5-68/120-862 MHz
- R female connector (Ø9.5 mm): 87.5-108 MHz
- SAT "F" type connector: 950-2400 MHz
- Recommended coaxial cable: 17/19 VATC
- Visual check of the connection
- Attenuation: 14 dB

**Male TV socket**

- TV: 0?862 MHz

**Caractéristiques générales**
**Valena™ IN'MATIC mechanisms - TV sockets**

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

**Documentation associée**

**Catalogue pages & additional information**

- [Description page \(p.499\)](#)
- [Selection chart \(p.509\)](#)
- [Selection chart \(p.513\)](#)
- [Valena, Synergy and MosaicTMProgramme - TV sockets](#)


**Installation & technical data**

- F02111EN-00


**Installation instructions & related documents**

- LE07425CD