

CAT. N° 7 530 62



## TERMINAL TV-R SOCKET VALENA IN'MATIC

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,547
Weight (g)	129,00

### Product characteristics

#### Terminal sockets

- Installation in case of maintenance
- Amplifier and a line balancing are recommended
- TV male connector (Ø9.5 mm): 5-68/120-862 MHz
- R female connector (Ø9.5 mm): 87.5-108 MHz
- SAT "F" type connector: 950-2400 MHz
- Recommended coaxial cable: 17/19 VATC
- Visual check of the connection
- 1 input with 1 resistance cap socket
- -10 dB

#### TV-R socket

- TV-R socket

### General characteristics

#### Valena™ IN'MATIC mechanisms - TV sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.509\)](#)

#### Installation & technical data

- [F02112EN-01](#)

#### Installation instructions & related documents

- [LE07425CD](#)