

CAT. N° 7 530 64


TERMINAL TV-R-SAT SOCKET VALENA IN'MATIC

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,547 |
| Weight (g) | 141,00 |

Product characteristics
Terminal sockets

- Installation in case of maintenance
- Amplifier and a line balancing are recommended
- TV male connector (Ø9.5 mm): 5-68/120-862 MHz
- R female connector (Ø9.5 mm): 87.5-108 MHz
- SAT "F" type connector: 950-2400 MHz
- Recommended coaxial cable: 17/19 VATC
- Visual check of the connection
- 1 input with 1 resistance cap socket
- -10 dB

TV-R-SAT socket

- TV: 5?68/120?862 MHz
- R: 87.5?108 MHz
- SAT: 950?2400 MHz

General characteristics
Valena™ IN'MATIC mechanisms - TV sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.499\)](#)
- [Selection chart \(p.509\)](#)
- [Selection chart \(p.513\)](#)
- [Valena, Synergy and MosaicTMProgamme - TV sockets](#)

 **Installation & technical data**

- [F02112EN-01](#)

 **Installation instructions & related documents**

- [LE07425CD](#)