

CAT. N° 7 532 52



TV-R-SAT STAR SOCKET VALENA LIFE - ATTENUATION 1.5 DB - IVORY

Pack (number of units)	5
Volume (dm ³)	2,668
Weight (g)	622,00

Product characteristics

Star architecture TV sockets

- For DVBT, Cablecast and satellite installation
- UHD TV compatible
- Class A shielded star socket LTE Ready (4G protected)
- Recommended coaxial cable: 17 VATC
- Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch)
- Visual check of the connection
- Meet EN 50083-4 and EN 50083-2 European directive
- TV male connector (Ø9.5 mm); 0-862 MHz
- R female connector (Ø9.5 mm): 87.5 - 108 MHz
- SAT "F" type connector: 950-2400 MHz

TV-R-SAT sockets

- Low attenuation: 1.5 dB
- Ivory

General characteristics

Valena™ Life - TV sockets with cover plate

- Valena In'Matic mechanisms supplied with cover plates and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation



Catalogue pages & additional information

- [Description page \(p.520\)](#)



Installation & technical data

- [F02112EN-00](#)



Installation instructions & related documents

- [LE07455CA](#)