

CAT. N° 7 551 14



WIRELESS POWER STATION WITH USB TYPE A VALENA IN'MATIC - WHITE VALENA ALLURE

Pack (number of units)	1
Volume (dm ³)	1,516
Weight (g)	286,00

Product characteristics

Type-A USB charging sockets

- For recharging portable devices
- Conform to IEC 62684-2011-01
- Surge protection greater than 1 kV
- Power supply standby mode consumption: less than 0.06 W
- Power supply AC/DC efficiency at highest level (VI)
- 2x2.5 mm² screw terminals
- Class II SELV
- Supplied cordless

Wireless power stations with Type-A USB

- 1 A charger with one 3 A/12 W USB port to power a second device
- To be fitted with a support and a plate
- Comes with 2 induction antennae for fast intuitive smartphone charging
- Recognition area: 50 x 80 mm
- Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging
- Dimensions: 136.5 x 70 x 56.5 mm
- Anti-theft lock function
- Can be mounted in multiple horizontal positions
- White Valena Allure

General characteristics

Valena™ IN'MATIC mechanisms - USB charging sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- IP 2X protection
- Supplied with mounted dust protection transparent shield
- Packaged in boxes (except Valena Life double USB charging socket - in flowpack)

Documentation

Catalogue pages & additional information

- [Description page \(p.504\)](#)
- [Valena™ IN'MATIC mechanisms - USB charging sockets](#)

Installation & technical data

- F02384EN-00

Installation instructions & related documents

- [LE09622AB](#)
- [LE09622AC](#)
- [LE09622AD](#)