

CAT. N° 7 551 97



## ILLUMINAT. MULTI. SWITCH VALENA ALLURE -SCREW/CLAW MOUNTING -10 AX -250 V~ -ALU

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Switches 10 AX - 250 V~

##### Illuminated multifunction switches

- Automatic terminals
- 5 functions = 1 Cat.No
- Supplied with 2 LEDs Cat.No 0 676 86, and single and double cover plates to create:
  - a two-way switch or a changeover push-button
  - an illuminated 2-gang two-way switch or an illuminated 2-gang changeover push-button
  - an illuminated two-way switch + illuminated changeover push-button (on the left or on the right)
  - Supplied in illuminated 2-gang changeover pushbutton mode, with fitted double cover plates, and an additional single cover plate
- Aluminium Valena Allure

### General characteristics

#### Valena™ IN'MATIC mechanisms - switches

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- Supplied with mounted dust protection transparent shield
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Packaged in boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.494\)](#)

#### Agreements & certificates of conformity

- [NF - NF012\\_1596](#)
- [OC / CB - FR\\_703340](#)

#### Installation instructions & related documents

- [LE08586AA](#)