

CAT. N° 7 554 08



LCD RDS TUNER VALENA - SOUND DIFFUSION - WITH POWER SUPPLY - BLACK

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Sound diffusion

LCD RDS tuners with power supply

- Ideal for bathroom, kitchen and bedroom. Supplied with cover plate
- Built-in 230 V power supply
- Manual or automatic station selection (RDS search)
- Stores 10 stations. Built-in aerial. Volume, balance and bass/treble control. Has an auxiliary input (3.5 mm Øjack) for connecting an MP3 player (lead not supplied). Compatible with 4/8 or 16 ohms loudspeakers except for Cat.No 0 673 30. Stereo or mono output. Output power 2 x 3 W. Station display, creation of 2 lists of favourites (2 x 8 presets)
- Alarm function (possible to set 2 different times). Loudspeaker selection (left or right) for each of the alarms
- Timer function
- On/off control (manual/automatic), presence of mains supply
- Supplied with Cat. No. 0 801 02 Batibox multimaterial 2-gang box (depth 40 mm)
- Product to be completed with 5-module plate (Valena Life or Valena Allure)
- Black Valena Allure

General characteristics

Valena™ IN'MATIC mechanisms - sound diffusion and loudspeakers

- Valena In'Matic mechanisms are with metal support, claw or screw mounting
- To be equipped with cover plates and plates of Valena Life or Valena Allure
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation



Catalogue pages & additional information

- Valena™ IN'MATIC mechanisms - sound diffusion



Installation instructions & related documents

- LE08589AA