

CAT. N° 7 646 94



DOUBLE USB CHARGING SOCKET NILOÉ - IVORY

| | |
|---------------------------|-------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,534 |
| Weight (g) | 98,00 |

Product characteristics

USB Type A charging sockets

- 5 V - 3 A - 12 W
- For recharging portable device
- Conform to IEC 62684-2011-01
- Surge protection greater than 1 kV
- Consumption in passive mode less than 0.06 W
- Power supply AC/DC efficiency at highest Level (VI)
- 2x2.5 mm² screw terminals
- Class II SELV
- Supplied cordless

Double USB sockets

- 2 modules
- For fast charging smartphones and tablet PC
- Ivory

General characteristics

Niloé™ - USB charging sockets

- Mechanisms supplied with support frame and cover plate
- Fixing with screws or claws (supplied)
- For installation in flush-mounting box depth 40 mm minimum
- Supplied cordless

Documentation

Catalogue pages & additional information

- [Description page \(p.536\)](#)
- [Technical page \(p.537\)](#)

Installation & technical data

- [F02165EN-01](#)