

CAT. N° 8 320 02



## SINGLE POLE PLATE SWITCH SYNERGY -2 GANG -2-WAY -10 AX -250 V~ SLEEK DESIGN BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	149,00

### Product characteristics

#### Single pole plate switches 10 AX - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm

#### 2 gang - 2-way switches

- Brushed stainless steel

### General characteristics

#### Synergy™ - single pole switches and dimmers - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.590\)](#)

#### Agreements & certificates of conformity

- [ASTA-781](#)
- [QC / CB-FR\\_708093](#)

#### Installation & technical data

- [F02254EN-01](#)