

CAT. N° 8 320 23



DOUBLE POLE SWITCH SYNERGY -BLUE LED -45 A -250 V~ SLEEK DESIGN BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	201,00

Product characteristics

Double pole switches 45 A - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 47 mm deep
- Red rocker
- Nominal plate dimensions: 86 x 86 mm

DP switches + blue LED power indicator

- Brushed stainless steel

General characteristics

Synergy™ - double pole switches - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.591\)](#)

Agreements & certificates of conformity

- [OC / CB-FR_708126](#)
- [ASTA-783](#)

Installation & technical data

- [F02258EN-00](#)